FARO Edge ScanArm ES

Features, Benefits & Technical Specifications





Enhanced Scanning Technology

 The FARO Edge ScanArm ES with new software algorithm enables users to effortlessly scan materials with challenging optical qualities

High Contrast Capture Mode

 New HDR Mode (High Dynamic Range) allow users to scan materials with high contrasting colors simultaneously

Intuitive On-Board Measurement System

- Built-in touchscreen computer
- Laptop-free basic measurements
- Personalized settings
- QuickTools
- On-board diagnostics

Smart Multi-Function Handle Port

- Seamless and interchangeable accessory integration
- Quick-change handle & expandable capability

Smart Connectivity

- Bluetooth®, Wi-Fi®, USB, and Ethernet ready
- Multiple device management through enhanced networking

Smart Sensor Technology

- Warn against excessive external loads
- Correct for thermal changes
- Detect possible setup problems

Multi-Probe Capability

- Use standard and custom probes
- FARO iProbe with automatic size recognition and temperature sensor

Non-Contact Measurement with Enhanced Scanning Technology

The FARO Edge ScanArm ES is the latest advancement in FARO's Laser Line Probe product line and features Enhanced Scanning Technology (EST). EST is the combination of multiple hardware and software improvements such as the High Dynamic Range (HDR) mode designed to boost performance by improving the ability to scan challenging surfaces including high contrasting colors simultaneously.

The FARO Edge ScanArm ES is the world's smallest, lightest, and affordable solution that combines the convenience of a FaroArm with the power of a Laser Line Probe to form the perfect contact/non-contact portable measurement system.

Most Common Applications

Aerospace: Reverse Engineering, Certification, Part Inspection
Automotive: Tool Building & Certification, Alignment, Part Inspection
Metal Fabrication: On-Machine Inspection, First Article inspection, Periodic Part Inspection
Molding/Tool & Die: Mold and Die Inspection, Prototype Part Scanning

Benefits

- ▶ Simplified user experience
- Quick measurements without a computer
- Improved reliability and capability
- Scan dark or reflective materials without special surface preparation
- Exceptional scanning speed up to 45,120 points per second

FARO Edge ScanArm ES



FARO Laser Line Probe Specifications

±35µm (±0.0014 in.) Accuracy: Repeatability: 35μm, 2σ (0.0014 in.)

Stand-off: 80mm (3.15 in.) Depth of field: 85mm (3.35 in.)

Effective scan width: Near field 53mm (2.09 in.)

Far field 90mm (3.54 in.)

Points per line: 752 points/line

60 frames/second x 752 points/line Scan rate:

= 45,120 points/sec.

Laser: 660nm, CDRH Class II/IEC Class 2M

Weight: 222.4g (0.49lbs.)

Performance Specifications

Contact

Model (Measuring Range)		Single Point Repeatability	Volumetric Accuracy	FaroArm Weight
Axis		7	7	7
Edge	1.8 m	0.024 mm	±0.034 mm	10.7 kg
	(6 ft)	(0.0009 in.)	(±0.0013 in.)	(23.6 lbs.)
Edge	2.7 m	0.029 mm	±0.041 mm	10.9 kg
	(9 ft)	(0.0011 in.)	(±0.0016 in.)	(24.1 lbs.)
Edge	3.7 m	0.064 mm	±0.091 mm	11.3 kg
	(12 ft)	(0.0025 in.)	(±0.0035 in.)	(24.9 lbs)

FaroArm test methods are a subset of those given in the B89.4.22 standard.

Single point articulation performance test (Max-Min)/2: The probe of the FaroArm is placed within a conical socket, and individual points are measured from multiple approach directions as specified by ASME the B89.4.22-2004 standard. Each individual point measurement is analyzed as a range of deviations in X, Y, Z. Volumetric Accuracy or Volumetric Maximum Deviation: Determined by using 20 traceable lengths measured at locations and orientations throughout the working volume of the FaroArm as specified by the ASME B89.4.22-2004 standard. This test is a method for determining articulated arm accuracy.

Hardware Specifications

10°C - 40°C (50°F - 104°F) Operating temp range:

Temperature rate: 3°C/5min. (5.4°F/5min.)

Operating humidity range: 95%, noncondensing

Power supply:

100-240VAC 47/63Hz

Universal worldwide voltage





Meets OSHA requirements, NRTL Listed, MET-C Listed, Complies with Electronic Code of Federal Regulations 47 CFR PART 15 and 21 CFR 1040 Performance standards For Light-Emitting Products.

Complies with the following EC Directives: 93/68/EEC CE Marking; 2004/108/EC ELECTRICAL EQUIPMENT; 1999/5/EC R&TTE Directive;

2002/95/EC - RoHS.

Conforms to the following standards: EN 61010-1:2001 / CSA-C22.2 No. 61010-1; EN 61326-1:2006; IEC 60825-1:2007; FDA (CDRH) 21 CFR 1040.10 / ANSI Z136.1-2007; IEEE 802.11 b/g; FCC Part 15 Subpart C / IC RSS-210

and ESTI EN 300/301 (WLAN and Bluetooth).

Patents: 5402582, 5611147, 5794356, 6366831, 6606539, 6904691, 6925722, 6935036, 6973734, 6988322, 7017275, 7032321, 7043847, 7051450, 7069664, 7269910, 7735234, 7784194, 7804602, 7881896,

RE42055, RE42082